


Product Presentation



Application

This tester applies to pedestal base chairs with casters or chairs with legs and casters, to evaluate the ability of the casters, chair frame or chair base to withstand fatigue stresses and wear caused by moving the chair back and forth.

Feature

- The machine frame is made of high quality aluminum, beautiful and generous
- Obstruction block can be dismantle freely, easy to switch test mode

Standards

EN1730

Key Specification

Modle	GT-LD03
Control method	PLC Touch screen control
Moving stroke	1 000 ± 100 mm
Obstacle block	Width: 50mm
	Thickness: 2mm
	2 pieces, 500mm apart
Driving method	Motor
Test speed	0.2m/s
Testing time	0~9999min, settable
Power supply	1 φ AC 220V 50Hz 5A